


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.60
A1	0.05	-	0.15
A2	1.35	1.40	1.45
D	15.75	16.00	16.25
D1	13.95	14.00	14.05
E	15.75	16.00	16.25
E1	13.95	14.00	14.05
Ø	0°	-	7°
c	-	-	0.20
b	0.30	0.35	0.40
L	0.45	0.60	0.75
e	0.80 TYP		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []