



Exposed thermal pad zone

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.1
A1	0.05	-	0.15
A2	0.85	0.9	0.95
D	4.9	5	5.1
E1	4.3	4.4	4.5
E	6.4 BSC		
D1	2.9	3	3.1
E2	2.9	3	3.1
θ	0°	-	8°
c	0.09	-	0.2
b	0.19	-	0.3
L	0.5	0.6	0.7
e	0.65 BSC		

1) Dimension 'D' does not include mold flash, protrusions or gate burrs. mold flash, protrusions or gate burrs shall not exceed 0.15 per side.

2) Dimension 'E1' does not include interlead flash or protrusion shall not exceed 0.25 per side.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensioning & tolerances per ASME. Y14.5M-1994.