


All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensions and tolerances methods per ASME Y14.5-2009.

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.45
A1	0.25	0.35	0.45
D	12 BSC		
E	12 BSC		
ϕb	0.35	0.45	0.55
eD	0.8 BSC		
eE	0.8 BSC		
SD / SE	0.4		