

# IRF9240

PD-90420B

## Repetitive Avalanche and $dv/dt$ Rated Power MOSFET Thru-Hole (TO-204AA) -200V, -11A, P-channel

### Features


- Repetitive avalanche ratings
- Dynamic  $dv/dt$  rating
- Hermetically sealed
- Simple drive requirements
- ESD rating: Class 2 per MIL-STD-750, Method 1020

### Potential Applications

- DC-DC converter
- Motor drives

### Product Summary

- $BV_{DSS}$ : -200V
- $I_D$ : -11A
- $R_{DS(on),max}$ :  $0.5\Omega$
- $Q_{G,max}$ : 60nC



### Product Validation

Adhered to JANTX screening flow according to MIL-PRF-19500 for high-reliability applications

### Description

HEXFET POWER MOSFET technology is the key to IR HiRel advanced line of power MOSFET transistors. The efficient geometry and unique processing of this latest “State of the Art” design achieves: very low on-state resistance combined with high transconductance; superior reverse energy and diode recovery  $dv/dt$  capability. The HEXFET transistors also feature all of the well-established advantages of MOSFETs such as voltage control, very fast switching and temperature stability of the electrical parameters. They are well suited for applications such as switching power supplies, motor controls, inverters, choppers, audio amplifiers and high energy pulse circuits.

### Ordering Information

**Table 1**      **Ordering options**

Part number	Package	Screening Level
IRF9240	TO-3 (TO-204AA)	COTS
IRF9240SCX	TO-3 (TO-204AA)	JANTX

**Table of contents**

**Table of contents**

<b>Features .....</b>	<b>1</b>
<b>Potential Applications.....</b>	<b>1</b>
<b>Product Validation.....</b>	<b>1</b>
<b>Description .....</b>	<b>1</b>
<b>Table of contents.....</b>	<b>2</b>
<b>1 Absolute Maximum Ratings .....</b>	<b>3</b>
<b>2 Device Characteristics .....</b>	<b>4</b>
2.1 Electrical Characteristics .....	4
2.2 Source-Drain Diode Ratings and Characteristics .....	5
2.3 Thermal Characteristics .....	5
<b>3 Electrical Characteristics Curves.....</b>	<b>6</b>
<b>4 Test Circuits .....</b>	<b>9</b>
<b>5 Package Outline .....</b>	<b>10</b>
<b>Revision history.....</b>	<b>11</b>

## Absolute Maximum Ratings

## 1 Absolute Maximum Ratings

Table 2 Absolute Maximum Ratings

Symbol	Parameter	Value	Unit
$I_{D1} @ V_{GS} = -10V, T_C = 25^\circ C$	Continuous Drain Current	-11	A
$I_{D2} @ V_{GS} = -10V, T_C = 100^\circ C$	Continuous Drain Current	-7.0	A
$I_{DM} @ T_C = 25^\circ C$	Pulsed Drain Current <sup>1</sup>	-44	A
$P_D @ T_C = 25^\circ C$	Maximum Power Dissipation	125	W
	Linear Derating Factor	1.0	W/°C
$V_{GS}$	Gate-to-Source Voltage	± 20	V
$E_{AS}$	Single Pulse Avalanche Energy <sup>2</sup>	500	mJ
$I_{AR}$	Avalanche Current <sup>1</sup>	-11	A
$E_{AR}$	Repetitive Avalanche Energy <sup>1</sup>	12.5	mJ
dv/dt	Peak Diode Reverse Recovery <sup>3</sup>	-5.0	V/ns
$T_J$ $T_{STG}$	Operating Junction and Storage Temperature Range	-55 to +150	°C
	Lead Temperature	300 (0.063 in. (1.6mm) from case for 10s)	
	Weight	11.5 (Typical)	g

<sup>1</sup> Repetitive Rating; Pulse width limited by maximum junction temperature.

<sup>2</sup>  $V_{DD} = -50V$ , starting  $T_J = 25^\circ C$ ,  $L = 8.26mH$ , Peak  $I_L = -11A$ ,  $V_{GS} = -10V$

<sup>3</sup>  $I_{SD} \leq -11A$ ,  $di/dt \leq -150A/\mu s$ ,  $V_{DD} \leq -200V$ ,  $T_J \leq 150^\circ C$

## Device Characteristics

## 2 Device Characteristics

### 2.1 Electrical Characteristics

**Table 3 Static and Dynamic Electrical Characteristics @  $T_j = 25^\circ\text{C}$  (Unless Otherwise Specified)**

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions
$BV_{DSS}$	Drain-to-Source Breakdown Voltage	-200	—	—	V	$V_{GS} = 0V, I_D = -1.0mA$
$\Delta BV_{DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	—	-0.20	—	V/ $^\circ\text{C}$	Reference to $25^\circ\text{C}$ , $I_D = -1.0mA$
$R_{DS(on)}$	Static Drain-to-Source On-State Resistance	—	—	0.50	$\Omega$	$V_{GS} = -10V, I_{D2} = -7.0A^1$
		—	—	0.58		$V_{GS} = -10V, I_{D2} = -11A^1$
$V_{GS(th)}$	Gate Threshold Voltage	-2.0	—	-4.0	V	$V_{DS} = V_{GS}, I_D = -250\mu A$
$G_{fs}$	Forward Transconductance	4.0	—	—	S	$V_{DS} = -15V, I_{D2} = -7.0A^1$
$I_{DSS}$	Zero Gate Voltage Drain Current	—	—	-25	$\mu A$	$V_{DS} = -160V, V_{GS} = 0V$
		—	—	-250		$V_{DS} = -160V, V_{GS} = 0V, T_J = 125^\circ\text{C}$
$I_{GSS}$	Gate-to-Source Leakage Forward	—	—	-100	nA	$V_{GS} = -20V$
	Gate-to-Source Leakage Reverse	—	—	100		$V_{GS} = 20V$
$Q_G$	Total Gate Charge	28	—	60	nC	$I_{D1} = -11A$
$Q_{GS}$	Gate-to-Source Charge	3.0	—	15		$V_{DS} = -100V$
$Q_{GD}$	Gate-to-Drain ('Miller') Charge	4.5	—	38		$V_{GS} = -10V$
$t_{d(on)}$	Turn-On Delay Time	—	—	35	ns	$I_{D1} = -11A^{**}$
$t_r$	Rise Time	—	—	85		$V_{DD} = -100V$
$t_{d(off)}$	Turn-Off Delay Time	—	—	85		$R_G = 9.1\Omega$
$t_f$	Fall Time	—	—	65		$V_{GS} = -10V$
$L_s + L_D$	Total Inductance	—	6.1	—	nH	Measured from Drain lead (6mm/0.25 in from package) to Source lead (6mm/0.25 in from package)
$C_{iss}$	Input Capacitance	—	1200	—	pF	$V_{GS} = 0V$
$C_{oss}$	Output Capacitance	—	570	—		$V_{DS} = -25V$
$C_{rss}$	Reverse Transfer Capacitance	—	81	—		$f = 1.0MHz$

\*\* Switching speed maximum limits are based on manufacturing test equipment and capability.

<sup>1</sup> Pulse width  $\leq 300 \mu s$ ; Duty Cycle  $\leq 2\%$

## Device Characteristics

## 2.2 Source-Drain Diode Ratings and Characteristics

**Table 4 Source-Drain Diode Characteristics**

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions
$I_S$	Continuous Source Current (Body Diode)	—	—	-11	A	
$I_{SM}$	Pulsed Source Current (Body Diode) <sup>1</sup>	—	—	-44	A	
$V_{SD}$	Diode Forward Voltage	—	—	-4.6	V	$T_J = 25^\circ\text{C}$ , $I_S = -11\text{A}$ , $V_{GS} = 0\text{V}$ <sup>2</sup>
$t_{rr}$	Reverse Recovery Time	—	270	440	ns	$T_J = 25^\circ\text{C}$ , $I_F = -11\text{A}$ , $V_{DD} \leq -50\text{V}$ $di/dt = -100\text{A}/\mu\text{s}$ <sup>2</sup>
$Q_{rr}$	Reverse Recovery Charge	—	4.8	—	$\mu\text{C}$	
$t_{on}$	Forward Turn-On Time	Intrinsic turn-on time is negligible (turn-on is dominated by $L_S+L_D$ )				

## 2.3 Thermal Characteristics

**Table 5 Thermal Resistance**

Symbol	Parameter	Min.	Typ.	Max.	Unit
$R_{\theta JC}$	Junction-to-Case	—	—	1.0	$^\circ\text{C}/\text{W}$
$R_{\theta JA}$	Junction-to-Ambient (Typical socket mount)	—	—	30	

<sup>1</sup> Repetitive Rating; Pulse width limited by maximum junction temperature.


<sup>2</sup> Pulse width  $\leq 300 \mu\text{s}$ ; Duty Cycle  $\leq 2\%$

**IRF9240**


**Power MOSFET Thru-Hole (TO-204AA)**

**Electrical Characteristics Curves**


**3 Electrical Characteristics Curves**




**Figure 1 Typical Output Characteristics**



**Figure 2 Typical Output Characteristics**



**Figure 3 Typical Transfer Characteristics**




**Figure 4 Normalized On-Resistance Vs. Temperature**


**IRF9240**

**Power MOSFET Thru-Hole (TO-204AA)**


**Electrical Characteristics Curves**




**Figure 5 Typical Capacitance Vs. Drain-to-Source Voltage**



**Figure 6 Typical Gate Charge Vs. Gate-to-Source Voltage**



**Figure 7 Typical Source-Drain Diode Forward Voltage**



**Figure 8 Maximum Safe Operating Area**




Figure 9 Maximum Drain Current Vs. Case Temperature

Figure 10 Maximum Avalanche Energy Vs. Junction Temperature





Figure 11 Maximum Effective Transient Thermal Impedance, Junction-to-Case




**IRF9240**  
**Power MOSFET Thru-Hole (TO-204AA)**

**Test Circuits**


**4 Test Circuits**




**Figure 12 Gate Charge Test Circuit**




**Figure 13 Gate Charge Waveform**




**Figure 14 Unclamped Inductive Test Circuit**



**Figure 15 Unclamped Inductive Waveform**



**Figure 16 Switching Time Test Circuit**




**Figure 17 Switching Time Waveforms**

Package Outline

5 Package Outline

Note: For the most updated package outline, please see the website: [TO-3 \(TO-204AA\)](#)



**Revision history**

**Revision history**

<b>Document version</b>	<b>Date of release</b>	<b>Description of changes</b>
	01/26/2001	Datasheet (PD-90420)
Rev A	07/08/2019	Updated based on ECN-1120_06844
Rev B	12/06/2024	Updated based on ECN-1120_10102

## Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2024-12-06**

**Published by**

**International Rectifier HiRel Products,  
Inc.**

**An Infineon Technologies company  
El Segundo, California 90245 USA**

**© 2024 Infineon Technologies AG.  
All Rights Reserved.**

**Do you have a question about this  
document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**Document reference**

## IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office ([www.infineon.com](http://www.infineon.com)).

## WARNINGS

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest International Rectifier HiRel Products, Inc., an Infineon Technologies company, office.

International Rectifier HiRel Components may only be used in life-support devices or systems with the expressed written approval of International Rectifier HiRel Products, Inc., an Infineon Technologies company, if failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety and effectiveness of that device or system.

Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.