

IRFE9130 (JANTX2N6849U)

PD-91716E

Repetitive Avalanche and dv/dt Rated Power MOSFET
Surface Mount (LCC-18)
-100V, -6.5A, P-channel

Features

- Surface mount
- Small footprint
- Alternative to TO-39 Package
- Hermetically sealed
- Dynamic dv/dt rating
- Avalanche energy rating
- Simple drive requirements
- Light weight
- ESD rating: Class 1C per MIL-STD-750, Method 1020

Product Summary

- BV_{DSS} : -100V
- I_D : -6.5A
- $R_{DS(on),max}$: 0.30Ω
- $Q_{G,max}$: 34.8nC
- REF: MIL-PRF-19500/564



Potential Applications

- DC-DC converter
- Motor drives

Product Validation

Qualified to JANTX screening flow according to MIL-PRF-19500 for high-reliability applications

Description

The leadless chip carrier (LCC) package represents the logical next step in the continual evolution of surface mount technology. Desinged to be a close replacement for the TO-39 package, the LCC will give designers the extra flexibility they need to increase circuit board density. IR HiRel has engineered the LCC package to meet the specific needs of the power market by increasing the size of the bottom source pad, thereby enhancing the thermal and electrical performance. The lid of the package is grounded to the source to reduce RF interference.

Ordering Information

Table 1 Ordering options

Part number	Package	Screening Level
IRFE9130	LCC-18	COTS
JANTX2N6849U	LCC-18	JANTX
JANTXV2N6849U	LCC-18	JANTXV

Table of contents**Table of contents**

Features	1
Potential Applications.....	1
Product Validation.....	1
Description	1
Table of contents.....	2
1 Absolute Maximum Ratings	3
2 Device Characteristics	4
2.1 Electrical Characteristics	4
2.2 Source-Drain Diode Ratings and Characteristics	5
2.3 Thermal Characteristics	5
3 Electrical Characteristics Curves.....	6
4 Test Circuits	9
5 Package Outline	10
Revision history.....	11

Absolute Maximum Ratings**1 Absolute Maximum Ratings****Table 2 Absolute Maximum Ratings**

Symbol	Parameter	Value	Unit
I_{D1} @ $V_{GS} = -10V$, $T_c = 25^\circ C$	Continuous Drain Current	-6.5	A
I_{D2} @ $V_{GS} = -10V$, $T_c = 100^\circ C$	Continuous Drain Current	-4.1	A
I_{DM} @ $T_c = 25^\circ C$	Pulsed Drain Current ¹	-25	A
P_D @ $T_c = 25^\circ C$	Maximum Power Dissipation	25	W
	Linear Derating Factor	0.20	W/ $^\circ C$
V_{GS}	Gate-to-Source Voltage	± 20	V
E_{AS}	Single Pulse Avalanche Energy ²	165	mJ
I_{AR}	Avalanche Current ¹	-6.5	A
E_{AR}	Repetitive Avalanche Energy ¹	2.5	mJ
dv/dt	Peak Diode Reverse Recovery ³	-5.5	V/ns
T_J T_{STG}	Operating Junction and Storage Temperature Range	-55 to +150	$^\circ C$
	Lead Temperature	300 (for 5s)	
	Weight	0.42 (Typical)	g

¹ Repetitive Rating; Pulse width limited by maximum junction temperature.² $V_{DD} = -25V$, starting $T_J = 25^\circ C$, Peak $I_L = -6.5A$ ³ $I_{SD} \leq -6.5A$, $di/dt \leq -390A/\mu s$, $V_{DD} \leq -100 V$, $T_J \leq 150^\circ C$, Suggested $R_g = 7.5\Omega$

Device Characteristics

2 Device Characteristics**2.1 Electrical Characteristics****Table 3 Static and Dynamic Electrical Characteristics @ $T_j = 25^\circ\text{C}$ (Unless Otherwise Specified)**

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions
BV_{DSS}	Drain-to-Source Breakdown Voltage	-100	—	—	V	$\text{V}_{\text{GS}} = 0\text{V}, \text{I}_D = -1.0\text{mA}$
$\Delta \text{BV}_{\text{DSS}}/\Delta T_j$	Breakdown Voltage Temp. Coefficient	—	-0.10	—	V/ $^\circ\text{C}$	Reference to 25°C , $\text{I}_D = -1.0\text{mA}$
$R_{\text{DS}(\text{on})}$	Static Drain-to-Source On-State Resistance	—	—	0.30	Ω	$\text{V}_{\text{GS}} = -10\text{ V}, \text{I}_{\text{D2}} = -4.1\text{A}$ ¹
		—	—	0.32		$\text{V}_{\text{GS}} = -10\text{ V}, \text{I}_{\text{D2}} = -6.5\text{A}$ ¹
$\text{V}_{\text{GS}(\text{th})}$	Gate Threshold Voltage	-2.0	—	-4.0	V	$\text{V}_{\text{DS}} = \text{V}_{\text{GS}}, \text{I}_D = -250\mu\text{A}$
I_{DSS}	Zero Gate Voltage Drain Current	—	—	-25	μA	$\text{V}_{\text{DS}} = -80\text{V}, \text{V}_{\text{GS}} = 0\text{V}$
		—	—	-250		$\text{V}_{\text{DS}} = -80\text{V}, \text{V}_{\text{GS}} = 0\text{V}, T_j = 125^\circ\text{C}$
I_{GSS}	Gate-to-Source Leakage Forward	—	—	-100	nA	$\text{V}_{\text{GS}} = -20\text{V}$
	Gate-to-Source Leakage Reverse	—	—	100		$\text{V}_{\text{GS}} = 20\text{V}$
Q_G	Total Gate Charge	—	—	34.8	nC	$\text{I}_{\text{D1}} = -6.5\text{A}$
Q_{GS}	Gate-to-Source Charge	—	—	6.8		$\text{V}_{\text{DS}} = -50\text{V}$
Q_{GD}	Gate-to-Drain ('Miller') Charge	—	—	23.1		$\text{V}_{\text{GS}} = -10\text{V}$
$t_{\text{d}(\text{on})}$	Turn-On Delay Time	—	—	60	ns	$\text{I}_{\text{D1}} = -6.5\text{A}^{**}$ $\text{V}_{\text{DD}} = -40\text{V}$ $\text{R}_G = 7.5\Omega$ $\text{V}_{\text{GS}} = -10\text{V}$
t_r	Rise Time	—	—	140		
$t_{\text{d}(\text{off})}$	Turn-Off Delay Time	—	—	140		
t_f	Fall Time	—	—	140		
$\text{L}_{\text{s}} + \text{L}_{\text{D}}$	Total Inductance	—	6.1	—	nH	Measured from the center of drain pad to center of source pad
C_{iss}	Input Capacitance	—	790	—	pF	$\text{V}_{\text{GS}} = 0\text{V}$ $\text{V}_{\text{DS}} = -25\text{V}$ $f = 1.0\text{MHz}$
C_{oss}	Output Capacitance	—	340	—		
C_{rss}	Reverse Transfer Capacitance	—	71	—		

** Switching speed maximum limits are based on manufacturing test equipment and capability.

¹ Pulse width $\leq 300\ \mu\text{s}$; Duty Cycle $\leq 2\%$

Device Characteristics**2.2 Source-Drain Diode Ratings and Characteristics****Table 4 Source-Drain Diode Characteristics**

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions
I_S	Continuous Source Current (Body Diode)	—	—	-6.5	A	
I_{SM}	Pulsed Source Current (Body Diode) ¹	—	—	-25	A	
V_{SD}	Diode Forward Voltage	—	—	-4.3	V	$T_J = 25^\circ\text{C}, I_S = -6.5\text{A}, V_{GS} = 0\text{V}$ ²
t_{rr}	Reverse Recovery Time	—	—	250	ns	$T_J = 25^\circ\text{C}, I_F = -6.5\text{A}, V_{DD} \leq -50\text{V}$ $dI/dt = -100\text{A}/\mu\text{s}$
Q_{rr}	Reverse Recovery Charge	—	2.0	—	μC	
t_{on}	Forward Turn-On Time	Intrinsic turn-on time is negligible (turn-on is dominated by $L_S + L_D$)				




2.3 Thermal Characteristics**Table 5 Thermal Resistance**

Symbol	Parameter	Min.	Typ.	Max.	Unit
$R_{\theta JC}$	Junction-to-Case	—	—	5.0	$^\circ\text{C}/\text{W}$
$R_{\theta J-PCB}$	Junction-to-PC Board (Soldered to a copper clad PC board)	—	—	19	




¹ Repetitive Rating; Pulse width limited by maximum junction temperature.² Pulse width $\leq 300\ \mu\text{s}$; Duty Cycle $\leq 2\%$

Electrical Characteristics Curves


3 Electrical Characteristics Curves

**Figure 3 Typical Transfer Characteristics****Figure 4 Normalized On-Resistance Vs. Temperature**

Electrical Characteristics Curves



Electrical Characteristics Curves



**Figure 9 Maximum Drain Current Vs.
Case Temperature**

**Figure 10 Maximum Avalanche Energy Vs.
Junction Temperature**




Figure 11 Maximum Effective Transient Thermal Impedance, Junction-to-Case

Test Circuits

4 Test Circuits




Figure 12 Gate Charge Test Circuit

Figure 13 Gate Charge Waveform




Figure 14 Unclamped Inductive Test Circuit

Figure 15 Unclamped Inductive Waveform





Figure 16 Switching Time Test Circuit

Figure 17 Switching Time Waveforms

Package Outline**5 Package Outline**

Note: For the most updated package outline, please see the website: [LCC-18](#)



Revision history**Revision history**

Document version	Date of release	Description of changes
	01/25/2001	Datasheet (PD-91716B)
Rev C	07/28/2015	Updated based on ECN-1120_03204
Rev D	02/17/2019	Updated based on ECN-1120_06822
Rev E	12/06/2024	Updated based on ECN-1120_10116

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2024-12-06

Published by

**International Rectifier HiRel Products,
Inc.**

**An Infineon Technologies company
El Segundo, California 90245 USA**

**© 2024 Infineon Technologies AG.
All Rights Reserved.**

**Do you have a question about this
document?**

Email: erratum@infineon.com

Document reference

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

WARNINGS

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest International Rectifier HiRel Products, Inc., an Infineon Technologies company, office.

International Rectifier HiRel Components may only be used in life-support devices or systems with the expressed written approval of International Rectifier HiRel Products, Inc., an Infineon Technologies company, if failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety and effectiveness of that device or system.

Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.