


- 1) Max 1% mold flash coverage at heatsink is allowed
 - 2) All metal surfaces tin plated except area of cut and heatsink
- All dimensions are in units mm
 The drawing is in compliance with ISO 128-30, Projection Method 1 []
 Drawing according to ISO 8015, general tolerances $\pm 0.1; \pm 1^\circ$