


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.4
A1	0.35	0.45	0.55
D	11 BSC		
E	9 BSC		
Øb	0.55	0.65	0.75
eE	1 BSC		
eD	1 BSC		
SD/SE	0.5 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensioning and tolerancing methods per ASME Y14.5M-1994.