


- 1) All metal surfaces: tin plated, except area of cut
- 2) (\*) shoulder width tolerance inclusive of cutting protrusion

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Drawing according to ISO 8015, general tolerances  $\pm 0,1$ ;  $\pm 1^\circ 30$