


All dimensions refer to JEDEC standard TO-247 and do not include mold flash or protrusions.

Pkg surface route between pin 1 & pin 2 will be 5.1mm min.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances ISO 2768-mK