


- 1) Does not include plastic or metal protrusion of 0.15 max. per side
 - 2) Does not include dambar protrusion of 0.08 max. in excess of leadwidth at max. material condition min. space between protrusion is 0.07mm
 - 3) Does not include plastic or metal protrusion of 0.25 max. per side
- All dimensions are in units mm
- The drawing is in compliance with ISO 128-30, Projection Method 1 []
- Drawing according to ISO 8015, general tolerances ISO 2768-mK