


Detail "C" option 1



Detail "C" option 2

| SYMBOL | DIMENSIONS |      |      |
|--------|------------|------|------|
|        | MIN.       | NOM. | MAX. |
| e      | 0.4 BSC    |      |      |
| N      | 48         |      |      |
| L      | 0.3        | 0.4  | 0.5  |
| b      | 0.15       | 0.2  | 0.25 |
| D2     | 4.5        | 4.6  | 4.7  |
| E2     | 4.5        | 4.6  | 4.7  |
| D      | 6 BSC      |      |      |
| E      | 6 BSC      |      |      |
| A      | -          | -    | 0.6  |
| A1     | 0          | -    | 0.05 |
| A3     | 0.152 Ref  |      |      |
| R      | 0.2 TYP    |      |      |
| K      | 0.3 MIN    |      |      |

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]