



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	0.80	0.85	0.90
A1	0.00	0.01	0.05
A2	0.60	0.65	0.70
A3		0.20 REF	
e		0.50 BSC	
N		56	
L	0.30	0.40	0.50
L1	0.05	0.15	0.25
b	0.20	0.25	0.30
b1	0.10	0.15	0.20

Dimensioning & tolerances conform to ASME Y14.5M. -1994.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 $\left[\begin{array}{c} \triangle \\ \oplus \end{array} \right]$