


All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensions and tolerances methods per ASME Y14.5-2009.

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.4
A1	0.25	0.35	0.45
D	9 BSC		
E	9 BSC		
$\text{Ø}b$	0.3	0.4	0.5
eD	0.65 BSC		
eE	0.65 BSC		