



Bottom view

327X

\varnothing	$\varnothing 0.15$	(M)	C	A	B
\varnothing	$\varnothing 0.08$	(M)	C		

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1.7
A1	0.3	-	-
D	17 BSC		
E	17 BSC		
$\varnothing b$	0.4	0.45	0.5
eD	0.8 BSC		
eE	0.8 BSC		
SD / SE	0.4 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensions and tolerances methods per ASME Y14.5-2009.