


1) Outer dimension does not include protrusion or intrusion of 0.15 per side  
 All dimensions are in units mm  
 The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]  
 Drawing according to ISO 8015, general tolerances ISO 2768-mk