


1) All metal surfaces tin plated except area of cut

2) Mold gate protrusion after degating.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances $\pm 0.1; \pm 1^\circ$