


1) +0.2 mm mold flash

All metal surfaces tin plated, except area of cut.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances $\pm 0.1 / \pm 1^\circ 30'$