


1) Typical metal surface min.  $x=7.25, y=6.9$

All metal surfaces: tin plated, except area of cut

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Drawing according to ISO 8015, general tolerances  $\pm 0.1, \pm 1^\circ 30'$