



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1
D	8 BSC		
E	8 BSC		
D2	2.9	3	3.1
E2	2.9	3	3.1
L	0.2	0.3	0.4
L1	0.3	0.4	0.5
L2	0.9	1	1.1
b	0.18	0.23	0.28
eT	0.5 BSC		
eR	0.6 BSC		
K	1.5	-	-

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []