



All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	0.8	0.9	1
A1	0	0.02	0.05
b	0.2	0.25	0.3
D	6 BSC		
E	6 BSC		
D1	4.6 BSC		
E1	4.6 BSC		
e	0.5 BSC		
L	0.325	0.4	0.475