



Detail "C" option 1



Detail "C" option 2

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
e	0.4 BSC		
N	68		
L	0.3	0.4	0.5
b	0.15	0.2	0.25
D2	5.6	5.7	5.8
E2	5.6	5.7	5.8
D	8 BSC		
E	8 BSC		
A	-	-	0.65
A1	0	-	0.05
A3 (Option 1)	0.203 Ref		
A3 (Option 2)	0.152 Ref		
R	0.2 TYP		
K	0.75 MIN		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]