


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
e	1.27 BSC.		
N	8		
L	0.55	0.6	0.65
b	0.35	0.4	0.45
D2	3.9	4	4.1
E2	3.3	3.4	3.5
D	5 BSC		
E	6 BSC		
A	0.45	0.5	0.55
A1	0	0.02	0.05
A3	0.2 REF		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Dimensioning and tolerancing conforms to ASME Y14.5M-1994.