



SYMBOL	DIMENSIONS		
	MIN	NOM	MAX
A	-	-	0.625
A1	0.207	0.21	0.213
A2	0.365 BSC		
A3	0.05 BSC		
A4	0.025 BSC		
D	2.15 BSC		
E	1.94 BSC		
$\varnothing b$	0.23	0.26	0.29
eD	0.4 BSC		
eE	0.4 BSC		
SD/SE	0 / 0.2 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Dimensions and tolerances methods per ASME Y14.5-2009.