


## Final datasheet

### Short circuit rugged 750 V EDT2 IGBT in reflow-solderable package co-packed with soft and fast recovery diode

#### Features

- $V_{CE} = 750\text{ V}$
- $I_C = 200\text{ A}$
- Suitable for 470 V  $V_{DC}$  systems and increased overvoltage margin for 400 V  $V_{DC}$  systems
- Very low  $V_{CEsat} = 1.4\text{ V}$  (typ.) at  $I_{Cnom} = 200\text{ A}$ , 25°C
- Short circuit robust  $t_{sc} = 5\text{ }\mu\text{s}$  at  $V_{CE} = 470\text{ V}$ ,  $V_{GE} = 15\text{ V}$
- Up to 40% less System  $R_{th}$  due to reflow capability, increased power output
- Self limiting current under short circuit condition
- Positive thermal coefficient and very tight parameter distribution for easy paralleling
- A Reduced number of parallel devices is required due to  $I_{nom} = 200\text{ A}$
- Excellent current sharing in parallel operation
- Smooth switching characteristics
- Low gate charge  $Q_G$
- Simple gate drive design
- Co-packed with fast soft recovery emitter controlled diode (Emcon3)
- Low EMI signature
- TO247PLUS package with high creepage distance
- High reliability and operating lifetime
- Resistive weldable pins for direct busbar connections



#### Potential applications

- xEV traction inverter
- DC-link discharge switch
- Automotive aux-drives


#### Product validation

- Qualified for automotive applications. Product Validation according to AEC-Q101
- Qualified Reflow device 260°C according to JEDEC J-STD-020 MSL2

#### Description

Package pin definition:

- Pin C & backside - collector
- Pin E - emitter
- Pin G - gate



Type	Package	Marking
AIQTB200N75CP2	PG-TO247-3-PLUS-NN8.5	AKQB20FCP

## Table of contents

	<b>Description</b> .....	1
	<b>Features</b> .....	1
	<b>Potential applications</b> .....	1
	<b>Product validation</b> .....	1
	<b>Table of contents</b> .....	2
<b>1</b>	<b>Package</b> .....	3
<b>2</b>	<b>IGBT</b> .....	3
<b>3</b>	<b>Diode</b> .....	5
<b>4</b>	<b>Characteristics diagrams</b> .....	7
<b>5</b>	<b>Package outlines</b> .....	14
<b>6</b>	<b>Testing conditions</b> .....	15
	<b>Revision history</b> .....	16
	<b>Disclaimer</b> .....	17

## 1 Package

**Table 1** Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Internal emitter inductance	$L_E$	simulated starting from L2 at 1 MHz		4.2		nH
Collector-emitter loop inductance	$L_{CE}$	simulated starting from L2 at 1 MHz		6		nH
Main emitter pin resistance	$R_E$	Simulated starting from L2 at 10 kHz		0.43		mΩ
Storage temperature	$T_{stg}$		-55		150	°C
Soldering temperature	$T_{sold}$	reflow soldering (MSL2 according to JEDEC J-STD-020)			260	°C
Thermal resistance, junction-ambient	$R_{th(j-a)}$				40	K/W
IGBT thermal resistance, junction-case	$R_{th(j-c)}$			0.12	0.16 <sup>1)</sup>	K/W
Diode thermal resistance, junction-case	$R_{th(j-c)}$			0.23	0.3 <sup>1)</sup>	K/W

1) Defined by simulation, not subject to production test

## 2 IGBT

**Table 2** Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit
Collector-emitter voltage	$V_{CE}$	$T_{vj} \geq 25\text{ °C}$	750	V
DC collector current, limited by $T_{vjmax}$	$I_C$	$T_c = 25\text{ °C}$	200	A
		$T_c = 100\text{ °C}$	200	
Pulsed collector current, $t_p$ limited by $T_{vjmax}$	$I_{Cpulse}$		600	A
Turn-off safe operating area		$V_{CE} \leq 750\text{ V}, T_{vj} \leq 175\text{ °C}$	600	A
Gate-emitter voltage	$V_{GE}$		±20	V
Transient gate-emitter voltage	$V_{GE}$	$t_p = 10\text{ }\mu\text{s}, D < 0.01$	±30	V
Short-circuit withstand time	$t_{SC}$	$V_{CC} \leq 470\text{ V}, V_{GE} = -8/15\text{ V}$ , Allowed number of short circuits < 1000, Time between short circuits $\geq 1.0\text{ s}, T_{vj} = 25\text{ °C}$	5	μs
Power dissipation	$P_{tot}$	$T_{vj} = 175\text{ °C}$		W
		$T_c = 25\text{ °C}$	938	
		$T_c = 100\text{ °C}$	469	

**Table 3** Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CEsat}$	$I_C = 200 \text{ A}, V_{GE} = 15 \text{ V}$	$T_{vj} = 25 \text{ }^\circ\text{C}$	1.2	1.4	1.55	V
			$T_{vj} = 175 \text{ }^\circ\text{C}$		1.7		
Gate-emitter threshold voltage	$V_{GETh}$	$I_C = 2.6 \text{ mA}, V_{CE} = V_{GE}$		5.2	5.8	6.4	V
Zero gate-voltage collector current	$I_{CES}$	$V_{CE} = 750 \text{ V}, V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ }^\circ\text{C}$			200	$\mu\text{A}$
			$T_{vj} = 175 \text{ }^\circ\text{C}$		6000		
Gate-emitter leakage current	$I_{GES}$	$V_{CE} = 0 \text{ V}, V_{GE} = 20 \text{ V}$				100	nA
Transconductance	$g_{fs}$	$I_C = 200 \text{ A}, V_{CE} = 20 \text{ V}$			143		S
Short-circuit collector current	$I_{SC}$	$V_{CC} \leq 470 \text{ V}, V_{GE} = -8/15 \text{ V}, t_{SC} \leq 5 \text{ } \mu\text{s}$ , Allowed number of short circuits < 1000, Time between short circuits $\geq 1.0 \text{ s}$ , $T_{vj} = 25 \text{ }^\circ\text{C}$			1250		A
Input capacitance	$C_{ies}$	$V_{CE} = 25 \text{ V}, V_{GE} = 0 \text{ V}, f = 100 \text{ kHz}$			20500		pF
Output capacitance	$C_{oes}$	$V_{CE} = 25 \text{ V}, V_{GE} = 0 \text{ V}, f = 100 \text{ kHz}$			540		pF
Reverse transfer capacitance	$C_{res}$	$V_{CE} = 25 \text{ V}, V_{GE} = 0 \text{ V}, f = 100 \text{ kHz}$			95		pF
Gate charge	$Q_G$	$V_{CC} = 600 \text{ V}, I_C = 200 \text{ A}, V_{GE} = -8/15 \text{ V}$			1270		nC
Turn-on delay time	$t_{d(on)}$	$V_{CC} = 470 \text{ V}, V_{GE} = -8/15 \text{ V}, R_{G(on)} = 5 \text{ } \Omega, R_{G(off)} = 5 \text{ } \Omega$	$T_{vj} = 25 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		89		ns
			$T_{vj} = 175 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		85		
Rise time (inductive load)	$t_r$	$V_{CC} = 470 \text{ V}, V_{GE} = -8/15 \text{ V}, R_{G(on)} = 5 \text{ } \Omega, R_{G(off)} = 5 \text{ } \Omega$	$T_{vj} = 25 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		120		ns
			$T_{vj} = 175 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		117		
Turn-off delay time	$t_{d(off)}$	$V_{CC} = 470 \text{ V}, V_{GE} = -8/15 \text{ V}, R_{G(on)} = 5 \text{ } \Omega, R_{G(off)} = 5 \text{ } \Omega$	$T_{vj} = 25 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		266		ns
			$T_{vj} = 175 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		284		
Fall time (inductive load)	$t_f$	$V_{CC} = 470 \text{ V}, V_{GE} = -8/15 \text{ V}, R_{G(on)} = 5 \text{ } \Omega, R_{G(off)} = 5 \text{ } \Omega$	$T_{vj} = 25 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		46		ns
			$T_{vj} = 175 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		60		
Turn-on energy <sup>1)</sup>	$E_{on}$	$V_{CC} = 470 \text{ V}, V_{GE} = -8/15 \text{ V}, R_{G(on)} = 5 \text{ } \Omega, R_{G(off)} = 5 \text{ } \Omega$	$T_{vj} = 25 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		15.3		mJ
			$T_{vj} = 175 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		16.3		

**(table continues...)**

**Table 3 (continued) Characteristic values**

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Turn-off energy	$E_{off}$	$V_{CC} = 470 \text{ V}, V_{GE} = -8/15 \text{ V}, R_{G(on)} = 5 \Omega, R_{G(off)} = 5 \Omega$	$T_{vj} = 25 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		7	mJ
			$T_{vj} = 175 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		8.1	
Total switching energy	$E_{ts}$	$V_{CC} = 470 \text{ V}, V_{GE} = -8/15 \text{ V}, R_{G(on)} = 5 \Omega, R_{G(off)} = 5 \Omega$	$T_{vj} = 25 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		22.3	mJ
			$T_{vj} = 175 \text{ }^\circ\text{C}, I_C = 200 \text{ A}$		24.4	
Operating junction temperature	$T_{vj}$		-40		175	$^\circ\text{C}$

1) includes IGBT losses caused by the reverse recovery current

### 3 Diode

**Table 4 Maximum rated values**

Parameter	Symbol	Note or test condition	Values	Unit	
Diode forward current, limited by $T_{vjmax}$	$I_F$		$T_c = 25 \text{ }^\circ\text{C}$	200	A
			$T_c = 100 \text{ }^\circ\text{C}$	200	
Diode pulsed current, $t_p$ limited by $T_{vjmax}$	$I_{Fpulse}$		600	A	
Power dissipation	$P_{tot}$	$T_{vj} = 175 \text{ }^\circ\text{C}$	$T_c = 25 \text{ }^\circ\text{C}$	500	W
			$T_c = 100 \text{ }^\circ\text{C}$	250	

**Table 5 Characteristic values**

Parameter	Symbol	Note or test condition	Values			Unit	
			Min.	Typ.	Max.		
Diode forward voltage	$V_F$	$I_F = 200 \text{ A}$	$T_{vj} = 25 \text{ }^\circ\text{C}$	1.6	1.8	2	V
			$T_{vj} = 175 \text{ }^\circ\text{C}$		1.9		
Diode reverse recovery charge	$Q_{rr}$	$V_R = 470 \text{ V}, R_{G(on)} = 5 \Omega$	$T_{vj} = 25 \text{ }^\circ\text{C}, I_F = 200 \text{ A}, -di_F/dt = 1060 \text{ A}/\mu\text{s}$		4.7		$\mu\text{C}$
			$T_{vj} = 175 \text{ }^\circ\text{C}, I_F = 200 \text{ A}, -di_F/dt = 1067 \text{ A}/\mu\text{s}$		7.5		

(table continues...)

Table 5 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit	
			Min.	Typ.	Max.		
Diode peak reverse recovery current	$I_{rrm}$	$V_R = 470 \text{ V}, R_{G(on)} = 5 \Omega$	$T_{vj} = 25 \text{ }^\circ\text{C},$ $I_F = 200 \text{ A},$ $-di_F/dt = 1060 \text{ A}/\mu\text{s}$		41		A
			$T_{vj} = 175 \text{ }^\circ\text{C},$ $I_F = 200 \text{ A},$ $-di_F/dt = 1067 \text{ A}/\mu\text{s}$		56		
Reverse recovery energy	$E_{rec}$	$V_R = 470 \text{ V}, R_{G(on)} = 5 \Omega,$ $L_\sigma = 50 \text{ nH}, C_\sigma = 30 \text{ pF}$	$T_{vj} = 25 \text{ }^\circ\text{C},$ $I_F = 200 \text{ A},$ $-di_F/dt = 1060 \text{ A}/\mu\text{s}$		1.1		mJ
			$T_{vj} = 175 \text{ }^\circ\text{C},$ $I_F = 200 \text{ A},$ $-di_F/dt = 1067 \text{ A}/\mu\text{s}$		1.9		
Operating junction temperature	$T_{vj}$		-40		175	$^\circ\text{C}$	

**Note:** For optimum lifetime and reliability, Infineon recommends operating conditions that do not exceed 80% of the maximum ratings stated in this datasheet.


Electrical Characteristic at  $T_{vj} = 25^\circ\text{C}$ , unless otherwise specified.

Dynamic test circuit, parasitic inductance  $L_\sigma = 50 \text{ nH}$ , parasitic capacitor  $C_\sigma = 30 \text{ pF}$  from Fig. E. Energy losses include "tail" and diode reverse recovery.

## 4 Characteristics diagrams


### Power dissipation as a function of case temperature

$P_{tot} = f(T_c)$   
 $T_{vj} \leq 175\text{ °C}$




### Collector current as a function of case temperature

$I_c = f(T_c)$   
 $T_{vj} \leq 175\text{ °C}, V_{GE} = 15\text{ V}$




### Typical output characteristic

$I_c = f(V_{CE})$   
 $T_{vj} = 25\text{ °C}$



### Typical output characteristic

$I_c = f(V_{CE})$   
 $T_{vj} = 175\text{ °C}$




4 Characteristics diagrams

**Typical transfer characteristic**

$I_C = f(V_{GE})$


$V_{CE} = 20 \text{ V}$



**Typical collector-emitter saturation voltage as a function of junction temperature**

$V_{CEsat} = f(T_{vj})$


$V_{GE} = 15 \text{ V}$



**Gate-emitter threshold voltage as a function of junction temperature**

$V_{GEth} = f(T_{vj})$


$I_C = 2.6 \text{ mA}$



**Typical switching times as a function of collector current**

$t = f(I_C)$

$V_{CC} = 470 \text{ V}, T_{vj} = 175^\circ\text{C}, V_{GE} = -8/15 \text{ V}, R_G = 5 \Omega$






4 Characteristics diagrams

**Typical switching times as a function of gate resistor**

$t = f(R_G)$


$I_C = 200\text{ A}, V_{CC} = 470\text{ V}, T_{vj} = 175\text{ }^\circ\text{C}, V_{GE} = -8/15\text{ V}$



**Typical switching times as a function of junction temperature**

$t = f(T_{vj})$


$I_C = 200\text{ A}, V_{CC} = 470\text{ V}, V_{GE} = -8/15\text{ V}, R_G = 5\text{ }\Omega$



**Typical switching energy losses as a function of collector current**

$E = f(I_C)$


$V_{CC} = 470\text{ V}, T_{vj} = 175\text{ }^\circ\text{C}, V_{GE} = -8/15\text{ V}, R_G = 5\text{ }\Omega$



**Typical switching energy losses as a function of gate resistor**

$E = f(R_G)$

$I_C = 200\text{ A}, V_{CC} = 470\text{ V}, T_{vj} = 175\text{ }^\circ\text{C}, V_{GE} = -8/15\text{ V}$




4 Characteristics diagrams

**Typical switching energy losses as a function of junction temperature**

$E = f(T_{vj})$


$I_C = 200\text{ A}$ ,  $V_{CC} = 470\text{ V}$ ,  $V_{GE} = -8/15\text{ V}$ ,  $R_G = 5\ \Omega$



**Typical switching energy losses as a function of collector emitter voltage**

$E = f(V_{CE})$


$I_C = 200\text{ A}$ ,  $V_{GE} = -8/15\text{ V}$ ,  $T_{vj} = 175\text{ °C}$ ,  $R_G = 5\ \Omega$



**Typical gate charge**

$V_{GE} = f(Q_G)$


$I_C = 200\text{ A}$



**Typical capacitance as a function of collector-emitter voltage**

$C = f(V_{CE})$


$f = 100\text{ kHz}$ ,  $V_{GE} = 0\text{ V}$



4 Characteristics diagrams


**Typical short circuit collector current as a function of gate-emitter voltage**

$I_{C(SC)} = f(V_{GE})$   
 $T_{vj} \leq 175\text{ }^{\circ}\text{C}, V_{CE} \leq 470\text{ V}$




**Short circuit withstand time as a function of gate-emitter voltage**

$t_{SC} = f(V_{GE})$   
 $T_{vj} \leq 175\text{ }^{\circ}\text{C}, V_{CE} \leq 470\text{ V}$




**IGBT transient thermal impedance as a function of pulse width**

$Z_{th(j-c)} = f(t_p)$   
 $D = t_p/T$



**Diode transient thermal impedance as a function of pulse width**


$Z_{th(j-c)} = f(t_p)$   
 $D = t_p/T$



4 Characteristics diagrams


**Typical diode forward current as a function of forward voltage**

$I_F = f(V_F)$



**Typical diode forward voltage as a function of junction temperature**


$V_F = f(T_{vj})$



**Typical reverse recovery time as a function of diode current slope**

$t_{rr} = f(di_F/dt)$


$V_R = 470\text{ V}, I_F = 200\text{ A}$



**Typical reverse recovery charge as a function of diode current slope**

$Q_{rr} = f(di_F/dt)$

$V_R = 470\text{ V}, I_F = 200\text{ A}$




**4 Characteristics diagrams**

**Typical reverse recovery current as a function of diode current slope**

$I_{rrm} = f(di_F/dt)$


$V_R = 470\text{ V}, I_F = 200\text{ A}$



**Typical diode peak rate of fall of reverse recovery current as a function of diode current slope**

$di_{rr}/dt = f(di_F/dt)$


$V_R = 470\text{ V}, I_F = 200\text{ A}$




**Typical reverse energy losses as a function of diode current slope**

$E_{rec} = f(di_F/dt)$

$V_R = 470\text{ V}, I_F = 200\text{ A}$



**5 Package outlines**



PACKAGE - GROUP  
 NUMBER: **PG-TO247-3-U02**


DIMENSIONS	MILLIMETERS	
	MIN.	MAX.
<b>A</b>	4.7	4.9
<b>A1</b>	2.16	2.66
<b>b</b>	1.2	
<b>b1</b>	1.8	
<b>b2</b>	2	
<b>b3</b>	0	0.15
<b>c</b>	0.5	0.7
<b>D</b>	15.7	15.9
<b>D1</b>	0.86	
<b>D2</b>	3.18	

DIMENSIONS	MILLIMETERS	
	MIN.	MAX.
<b>D3</b>	3.94	
<b>D4</b>	12.38	
<b>E</b>	22.7	22.9
<b>E1</b>	14.79	
<b>e</b>	5.44	
<b>H</b>	1.3	1.5
<b>L</b>	18.01	18.21
<b>L1</b>	2.44	
<b>L2</b>	2.36	
<b>aaa</b>	0.25	

- 1) All metal surfaces tin plated except area of cut
  - 2) Mold gate protrusion after degating
- All dimensions are in units mm  
 The drawing is in compliance with ISO 128-30, Projection Method 3 [⊕] [A]  
 Drawing according to ISO 8015, general tolerances

**Figure 1**

**6 Testing conditions**



**Figure 2**

**Revision history**

<b>Document revision</b>	<b>Date of release</b>	<b>Description of changes</b>
0.10	2023-02-21	Target datasheet
0.20	2024-02-22	Preliminary datasheet
1.00	2024-07-24	Final datasheet



## Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2024-07-25**

**Published by**

**Infineon Technologies AG**

**81726 Munich, Germany**

**© 2024 Infineon Technologies AG**

**All Rights Reserved.**

**Do you have a question about any aspect of this document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**Document reference**

**IFX-ABE861-003**

## Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

## Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.