

### 600 V Reverse Conducting Drive 2 offering cost effective IGBT with monolithically integrated diode

#### Features

- $V_{CE} = 600\text{ V}$
- $I_C = 6\text{ A}$
- Very tight parameter distribution
- Operating range of 1 to 20 kHz
- Maximum junction temperature  $150^\circ\text{C}$
- Short circuit capability of  $3\ \mu\text{s}$
- Humidity robust design
- Pb-free lead plating; RoHS compliant
- Complete product spectrum and PSpice Models: <http://www.infineon.com/rc-d2>

#### Potential applications

- Ceiling fan
- Countertop appliances - mixing
- Kitchen hood
- Refrigerators
- Residential aircon indoor unit
- Washing machines
- General purpose drives (GPD)


#### Product validation

- Qualified for industrial applications according to the relevant tests of JEDEC47/20/22

#### Description



- Green
- Halogen-free
- RoHS



Type	Package	Marking
IKN06N60RC2	PG-SOT223-3	K6DRC2

## Table of contents

	<b>Description</b> .....	1
	<b>Features</b> .....	1
	<b>Potential applications</b> .....	1
	<b>Product validation</b> .....	1
	<b>Table of contents</b> .....	2
<b>1</b>	<b>Package</b> .....	3
<b>2</b>	<b>IGBT</b> .....	3
<b>3</b>	<b>Diode</b> .....	5
<b>4</b>	<b>Characteristics diagrams</b> .....	7
<b>5</b>	<b>Package outlines</b> .....	14
<b>6</b>	<b>Testing conditions</b> .....	15
	<b>Revision history</b> .....	16
	<b>Disclaimer</b> .....	17

## 1 Package

**Table 1** Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Storage temperature	$T_{stg}$		-55		150	°C
Soldering temperature	$T_{sold}$	wave soldering / reflow soldering (MSL1 according to JEDEC J-STA-020)			260	°C
Thermal resistance, min. footprint junction-ambient	$R_{th(j-a)}$				160	K/W
Thermal resistance, 6 cm <sup>2</sup> Cu on PCB junction to ambient	$R_{th(j-a)}$				75	K/W
IGBT thermal resistance, junction-case <sup>1)</sup>	$R_{th(j-c)}$				17.3	K/W
Diode thermal resistance, junction-case <sup>1)</sup>	$R_{th(j-c)}$				24.4	K/W

1)  $R_{th}/Z_{th}$  based on single cooling pulse. Please be aware that a correct  $R_{th}$  measurement of the IGBT, is not possible using a thermocouple.

## 2 IGBT

**Table 2** Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit	
Collector-emitter voltage	$V_{CE}$	$T_{vj} \geq 25\text{ °C}$	600	V	
DC collector current, limited by $T_{vjmax}$ <sup>1)</sup>	$I_C$		$T_c = 25\text{ °C}$	8	A
			$T_c = 100\text{ °C}$	5.6	
Pulsed collector current, $t_p$ limited by $T_{vjmax}$	$I_{Cpulse}$		18	A	
Turn-off safe operating area		$V_{CE} \leq 600\text{ V}$ , $t_p = 1\text{ }\mu\text{s}$ , $T_{vj} \leq 150\text{ °C}$	18	A	
Gate-emitter voltage	$V_{GE}$		$\pm 20$	V	
Transient gate-emitter voltage	$V_{GE}$	$t_p \leq 10\text{ }\mu\text{s}$ , $D < 0.01$	$\pm 30$	V	
Short-circuit withstand time	$t_{SC}$	$V_{CC} \leq 400\text{ V}$ , $V_{GE} = 15\text{ V}$ , Allowed number of short circuits < 1000, Time between short circuits $\geq 1.0\text{ s}$ , $T_{vj} = 150\text{ °C}$	3	$\mu\text{s}$	
Power dissipation	$P_{tot}$		$T_c = 25\text{ °C}$	7.2	W
			$T_c = 100\text{ °C}$	2.9	

1) DPAK equivalent

**Table 3** Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CEsat}$	$I_C = 6\text{ A}, V_{GE} = 15\text{ V}$	$T_{vj} = 25\text{ °C}$		2	2.3	V
			$T_{vj} = 150\text{ °C}$		2.3		
Gate-emitter threshold voltage	$V_{GETh}$	$I_C = 65\text{ }\mu\text{A}, V_{CE} = V_{GE}$		4.3	5	5.7	V
Zero gate-voltage collector current	$I_{CES}$	$V_{CE} = 600\text{ V}, V_{GE} = 0\text{ V}$	$T_{vj} = 25\text{ °C}$			25	$\mu\text{A}$
			$T_{vj} = 150\text{ °C}$			2500	
Gate-emitter leakage current	$I_{GES}$	$V_{CE} = 0\text{ V}, V_{GE} = 20\text{ V}$				100	nA
Transconductance	$g_{fs}$	$I_C = 6\text{ A}, V_{CE} = 20\text{ V}$			2.5		S
Input capacitance	$C_{ies}$	$V_{CE} = 25\text{ V}, V_{GE} = 0\text{ V}, f = 1000\text{ kHz}$			250		pF
Output capacitance	$C_{oes}$	$V_{CE} = 25\text{ V}, V_{GE} = 0\text{ V}, f = 1000\text{ kHz}$			13		pF
Reverse transfer capacitance	$C_{res}$	$V_{CE} = 25\text{ V}, V_{GE} = 0\text{ V}, f = 1000\text{ kHz}$			10		pF
Gate charge	$Q_G$	$I_C = 6\text{ A}, V_{CC} = 480\text{ V}, V_{GE} = 15\text{ V}$			31		nC
Turn-on delay time	$t_{d(on)}$	$V_{CC} = 400\text{ V}, V_{GE} = 0/15\text{ V}, R_{Gon} = 49\text{ }\Omega, R_{Goff} = 49\text{ }\Omega, L_\sigma = 30\text{ nH}, C_\sigma = 32\text{ pF}$	$T_{vj} = 25\text{ °C}, I_C = 6\text{ A}$		8.8		ns
			$T_{vj} = 150\text{ °C}, I_C = 6\text{ A}$		9.2		
Rise time (inductive load)	$t_r$	$V_{CC} = 400\text{ V}, V_{GE} = 0/15\text{ V}, R_{Gon} = 49\text{ }\Omega, R_{Goff} = 49\text{ }\Omega, L_\sigma = 30\text{ nH}, C_\sigma = 32\text{ pF}$	$T_{vj} = 25\text{ °C}, I_C = 6\text{ A}$		13		ns
			$T_{vj} = 150\text{ °C}, I_C = 6\text{ A}$		13.4		
Turn-off delay time	$t_{d(off)}$	$V_{CC} = 400\text{ V}, V_{GE} = 0/15\text{ V}, R_{Gon} = 49\text{ }\Omega, R_{Goff} = 49\text{ }\Omega, L_\sigma = 30\text{ nH}, C_\sigma = 32\text{ pF}$	$T_{vj} = 25\text{ °C}, I_C = 6\text{ A}$		174		ns
			$T_{vj} = 150\text{ °C}, I_C = 6\text{ A}$		189		
Fall time (inductive load)	$t_f$	$V_{CC} = 400\text{ V}, V_{GE} = 0/15\text{ V}, R_{Gon} = 49\text{ }\Omega, R_{Goff} = 49\text{ }\Omega, L_\sigma = 30\text{ nH}, C_\sigma = 32\text{ pF}$	$T_{vj} = 25\text{ °C}, I_C = 6\text{ A}$		11.8		ns
			$T_{vj} = 150\text{ °C}, I_C = 6\text{ A}$		23.6		
Turn-on energy	$E_{on}$	$V_{CC} = 400\text{ V}, V_{GE} = 0/15\text{ V}, R_{Gon} = 49\text{ }\Omega, R_{Goff} = 49\text{ }\Omega, L_\sigma = 30\text{ nH}, C_\sigma = 32\text{ pF}$	$T_{vj} = 25\text{ °C}, I_C = 6\text{ A}$		151		$\mu\text{J}$
			$T_{vj} = 150\text{ °C}, I_C = 6\text{ A}$		207		
Turn-off energy	$E_{off}$	$V_{CC} = 400\text{ V}, V_{GE} = 0/15\text{ V}, R_{Gon} = 49\text{ }\Omega, R_{Goff} = 49\text{ }\Omega, L_\sigma = 30\text{ nH}, C_\sigma = 32\text{ pF}$	$T_{vj} = 25\text{ °C}, I_C = 6\text{ A}$		104		$\mu\text{J}$
			$T_{vj} = 150\text{ °C}, I_C = 6\text{ A}$		128		
Total switching energy	$E_{ts}$	$V_{CC} = 400\text{ V}, V_{GE} = 0/15\text{ V}, R_{Gon} = 49\text{ }\Omega, R_{Goff} = 49\text{ }\Omega, L_\sigma = 30\text{ nH}, C_\sigma = 32\text{ pF}$	$T_{vj} = 25\text{ °C}, I_C = 6\text{ A}$		255		$\mu\text{J}$
			$T_{vj} = 150\text{ °C}, I_C = 6\text{ A}$		355		

(table continues...)

**Table 3 (continued) Characteristic values**

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Operating junction temperature	$T_{vj}$		-40		150	°C

Note: Electrical Characteristic, at  $T_{vj} = 25^{\circ}\text{C}$ , unless otherwise specified

### 3 Diode

**Table 4 Maximum rated values**

Parameter	Symbol	Note or test condition	Values	Unit	
Repetitive peak reverse voltage	$V_{RRM}$	$T_{vj} \geq 25^{\circ}\text{C}$	600	V	
Diode forward current, limited by $T_{vjmax}$ <sup>1)</sup>	$I_F$		$T_c = 25^{\circ}\text{C}$	5.6	A
			$T_c = 100^{\circ}\text{C}$	2.5	
Diode pulsed current, $t_p$ limited by $T_{vjmax}$	$I_{Fpulse}$		18	A	

1) DPAK equivalent

**Table 5 Characteristic values**

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Diode forward voltage	$V_F$	$I_F = 6\text{ A}$	$T_{vj} = 25^{\circ}\text{C}$	1.85	2.2	V
			$T_{vj} = 150^{\circ}\text{C}$	1.9		
Diode reverse recovery time	$t_{rr}$	$V_R = 400\text{ V}$	$T_{vj} = 25^{\circ}\text{C}$ , $I_F = 6\text{ A}$ , $-di_F/dt = 535\text{ A}/\mu\text{s}$	42		ns
			$T_{vj} = 150^{\circ}\text{C}$ , $I_F = 6\text{ A}$ , $-di_F/dt = 509\text{ A}/\mu\text{s}$	106		
Diode reverse recovery charge	$Q_{rr}$	$V_R = 400\text{ V}$	$T_{vj} = 25^{\circ}\text{C}$ , $I_F = 6\text{ A}$ , $-di_F/dt = 535\text{ A}/\mu\text{s}$	0.123		$\mu\text{C}$
			$T_{vj} = 150^{\circ}\text{C}$ , $I_F = 6\text{ A}$ , $-di_F/dt = 509\text{ A}/\mu\text{s}$	0.357		
Diode peak reverse recovery current	$I_{rrm}$	$V_R = 400\text{ V}$	$T_{vj} = 25^{\circ}\text{C}$ , $I_F = 6\text{ A}$ , $-di_F/dt = 535\text{ A}/\mu\text{s}$	5.4		A
			$T_{vj} = 150^{\circ}\text{C}$ , $I_F = 6\text{ A}$ , $-di_F/dt = 509\text{ A}/\mu\text{s}$	7.2		

(table continues...)

**Table 5 (continued) Characteristic values**


Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Diode peak rate of fall of reverse recovery current	$di_{rr}/dt$	$V_R = 400 \text{ V}$	$T_{vj} = 25 \text{ °C}, I_F = 6 \text{ A},$ $-di_F/dt = 535 \text{ A}/\mu\text{s}$		190		A/ $\mu\text{s}$
			$T_{vj} = 150 \text{ °C},$ $I_F = 6 \text{ A},$ $-di_F/dt = 509 \text{ A}/\mu\text{s}$		71.5		
Operating junction temperature	$T_{vj}$			-40		150	°C

*Note: For optimum lifetime and reliability, Infineon recommends operating conditions that do not exceed 80% of the maximum ratings stated in this datasheet.*

## 4 Characteristics diagrams


### Power dissipation as a function of heatsink temperature

$P_{\text{tot}} = f(T_c)$   
 $T_{\text{vj}} \leq 150\text{ }^\circ\text{C}$




### Collector current as a function of heatsink temperature

$I_C = f(T_c)$   
 $T_{\text{vj}} \leq 150\text{ }^\circ\text{C}, V_{\text{GE}} \geq 15\text{ V}$




### Typical output characteristic

$I_C = f(V_{\text{CE}})$   
 $T_{\text{vj}} = 25\text{ }^\circ\text{C}$



### Typical output characteristic


$I_C = f(V_{\text{CE}})$   
 $T_{\text{vj}} = 150\text{ }^\circ\text{C}$



**Typical transfer characteristic**

$I_C = f(V_{GE})$


$V_{CE} = 20 \text{ V}$



**Typical collector-emitter saturation voltage as a function of junction temperature**

$V_{CEsat} = f(T_{vj})$


$V_{GE} = 15 \text{ V}$



**Gate-emitter threshold voltage as a function of junction temperature**

$V_{GEth} = f(T_{vj})$


$I_C = 65 \mu\text{A}$



**Typical switching times as a function of collector current**

$t = f(I_C)$

$V_{CC} = 400 \text{ V}, T_{vj} = 150^\circ\text{C}, V_{GE} = 0/15 \text{ V}, R_G = 49 \Omega$






4 Characteristics diagrams

**Typical switching times as a function of gate resistor**

$t = f(R_G)$


$I_C = 6 \text{ A}, V_{CC} = 400 \text{ V}, T_{vj} = 150 \text{ }^\circ\text{C}, V_{GE} = 0/15 \text{ V}$



**Typical switching times as a function of junction temperature**

$t = f(T_{vj})$


$I_C = 6 \text{ A}, V_{CC} = 400 \text{ V}, V_{GE} = 0/15 \text{ V}, R_G = 49 \text{ } \Omega$



**Typical switching energy losses as a function of collector current**

$E = f(I_C)$


$V_{CC} = 400 \text{ V}, T_{vj} = 150 \text{ }^\circ\text{C}, V_{GE} = 0/15 \text{ V}, R_G = 49 \text{ } \Omega$



**Typical switching energy losses as a function of gate resistor**

$E = f(R_G)$

$I_C = 6 \text{ A}, V_{CC} = 400 \text{ V}, T_{vj} = 150 \text{ }^\circ\text{C}, V_{GE} = 0/15 \text{ V}$




4 Characteristics diagrams

**Typical switching energy losses as a function of junction temperature**

$E = f(T_{vj})$


$I_C = 6 \text{ A}, V_{CC} = 400 \text{ V}, V_{GE} = 0/15 \text{ V}, R_G = 49 \Omega$



**Typical switching energy losses as a function of collector emitter voltage**

$E = f(V_{CE})$


$I_C = 6 \text{ A}, T_{vj} = 150 \text{ °C}, V_{GE} = 0/15 \text{ V}, R_G = 49 \Omega$



**Typical gate charge**

$V_{GE} = f(Q_G)$


$I_C = 6 \text{ A}$



**Typical capacitance as a function of collector-emitter voltage**

$C = f(V_{CE})$


$f = 1000 \text{ kHz}, V_{GE} = 0 \text{ V}$



4 Characteristics diagrams


**Typical short circuit collector current as a function of gate-emitter voltage**

$I_{C(SC)} = f(V_{GE})$   
 $T_{vj} \leq 150\text{ }^\circ\text{C}, V_{CC} \leq 400\text{ V}$




**IGBT transient thermal impedance as a function of pulse width**

$Z_{th(j-c)} = f(t_p)$   
 $D = t_p/T$




**Diode transient thermal impedance as a function of pulse width**

$Z_{th(j-c)} = f(t_p)$   
 $D = t_p/T$



**Typical diode forward current as a function of forward voltage**


$I_F = f(V_F)$



4 Characteristics diagrams

**Typical diode forward voltage as a function of junction temperature**


$V_F = f(T_{vj})$



**Typical reverse recovery time as a function of diode current slope**

$t_{rr} = f(di_F/dt)$


$V_R = 400$  V,  $I_F = 6$  A



**Typical reverse recovery charge as a function of diode current slope**

$Q_{rr} = f(di_F/dt)$


$V_R = 400$  V,  $I_F = 6$  A



**Typical reverse recovery current as a function of diode current slope**

$I_{rr} = f(di_F/dt)$


$V_R = 400$  V,  $I_F = 6$  A



**Typical diode peak rate of fall of reverse recovery current as a function of diode current slope**


$$di_{rr}/dt = f(di_F/dt)$$

$V_R = 400 \text{ V}$ ,  $I_F = 6 \text{ A}$



**5 Package outlines**

**PG-SOT223-3**



NOTES:  
 1. ALL DIMENSIONS REFER TO JEDEC STANDARD TO-261

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	1.52	1.80	0.060	0.071
A1	-	0.10	-	0.004
A2	1.50	1.70	0.059	0.067
b	0.60	0.80	0.024	0.031
b2	2.95	3.10	0.116	0.122
c	0.24	0.32	0.009	0.013
D	6.30	6.70	0.248	0.264
E	6.70	7.30	0.264	0.287
E1	3.30	3.70	0.130	0.146
e	2.3 BASIC		0.091 BASIC	
e1	4.6 BASIC		0.181 BASIC	
L	0.75	1.10	0.030	0.043
N	3		3	
O	0°	10°	0°	10°

<b>DOCUMENT NO.</b> Z8B00180553
<b>SCALE</b> 
<b>EUROPEAN PROJECTION</b> 
<b>ISSUE DATE</b> 24-02-2016
<b>REVISION</b> 01

**Figure 1**

**6 Testing conditions**



**Figure 2**

## Revision history

Document revision	Date of release	Description of changes
1.00	2021-10-01	Final datasheet
1.01	2021-10-15	Change of Potential Applications
1.10	2022-09-21	Add of wave soldering conditions



## Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

**Edition 2022-09-21**

**Published by**

**Infineon Technologies AG**

**81726 Munich, Germany**

**© 2022 Infineon Technologies AG**

**All Rights Reserved.**

**Do you have a question about any aspect of this document?**

**Email: [erratum@infineon.com](mailto:erratum@infineon.com)**

**Document reference**

**IFX-ABB691-003**

## Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

## Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.